


## Multi-Torque Vane Motors


### MHT Series 380 Thru 460

Model	Shaft	Snap Ring (2 req'd)	Key	Bearing (2 req'd)	Ring "A"	Ring "B"	Plug
MHT-380/190/190-*1-30	377512	354386	332265	310539	364468	364468	7074
MHT-440/250/190-*1-30					375223	375223	
MHT-500/250/250-*1-30					343826	343826	
MHT-410/220/190-N1-30	—	—	—	—	375223	364468	—
MHT-470/250/220-N1-30					343826	343826	
MHT-460/250/210-N1-30-S19					405171	405171	



# Model Code

**MHT \*\*\*/\*\*\*/\*\*\* - (\*) 1 30 - (S19)**



**1 Model Series**

High torque, low speed vane motor

**3 Shaft**

**N** - No shaft and bearings  
**R** - Solid shaft

**5 Design**

**6 Denote Special**

**2 Combination of Theoretical Torque in Lb.-Ft. per 100 P.S.I. Differential Pressure**

380/190/190  
 410/220/190  
 440/250/190  
 460/250/210  
 470/250/220  
 500/250/250

**4 Keyed Shaft**

(When provided)

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 18/15 or cleaner. Selections from pressure, return, and in-line filter series are recommended.