



COBRA® FLEX 20 NYLON

Note

Available with two or four extruded identification stripes moulded into the wall of the tube, but not extending to the inner surface. Colours available are red, yellow, brown, orange, dark blue, light green, pink, violet, black and grey.

Material

Co-extruded two-layer structure: nylon inner layer with flexible outer layer.

Quality Assurance

The tube is manufactured under ISO 9001:2000.

Approvals

SK ; Coca Cola; NSF

Application

Widely used beer line where extended cleaning is required. Also used as barrier gas line due to high resistance to porosity of gases. Will accept Cobrafit push-in fittings and similar.

Standard Tube Sizes

6.7mm x 9.5mm	0.265" x 0.375"
8.5mm x 11.5mm	0.335" x 0.453"
9.5mm x 12.7mm	0.375" x 0.500"

Packaging:

Available in coils: 30m, 100m

COBRA® FLEX nylon tubing complies with EC Statutory Instrument 1992 No. 3145 and Brewers & Licensed Retailers' Association (formerly the Brewers' Society) Standard QAS 3244.

Chemical Resistance

For suitability of natural nylon tube in contact with various chemicals, please refer to the data sheet "Chemical Resistance of Plastics".