

Horticultural Spray Tubing

4233 Horticultural Spray Tubing



Features

- Core Tube Resists Hydrocarbon Deposit Build-up
- Offers Excellent Kink Resistance, Good Resistance to Vacuum Collapse
- Lightweight for Easier Handling
- Provides Higher Temperature Resistance and Excellent Flexibility
- Contains Three Flexible Layers for Maximum Flexibility

Applications

- Weed Spray Control
- Horticultural Spray

Construction

- Bonded Co-Extruded Nylon Polyethylene Construction

Part Number	Nominal I.D.		Nominal O.D.		Wall Thickness		Minimum Burst Pressure 75°F (23.9°C)		Weight	
	in	mm	in	mm	in	mm	psi	bar	lbs/ 100 ft	kg/ 100 m
	4233-0450	1/4	6.4	.350	8.9	.050	1.3	800	55	3.17
4233-0550	5/16	8.1	.420	10.7	.050	1.3	800	55	4.05	6.0
4233-0662	3/8	9.5	.500	12.7	.062	1.6	800	55	4.75	7.1
4233-0768	7/16	11.1	.574	14.6	.068	1.7	800	55	5.25	7.8
4233-0875	1/2	13.0	.650	16.5	.075	1.9	250	17	6.5	9.6

Exhaust Gas Analyzer Tubing

4262 Exhaust Gas Analyzer Tubing



Features

- Temperature Range: -40°F to 200°F (-40°C to 93°C)
- Smooth Core Tube Resists Hydrocarbon Deposit Buildup
- Special Polymer Cover Provides Excellent Temperature Resistance
- Very Flexible, Flame Retardant
- Bonded Co-Extruded Construction for Kink Resistance
- Resistant to Vacuum Collapse

Applications

- Emissions Analysis
- Low Pressure Pneumatics
- Low Pressure Chemical Transfer
- Vacuum Applications

Construction

- Proprietary Black Polymer Exterior
- Nylon Lined

Part Number	Nominal I.D.		Nominal O.D.		Wall Thickness		Minimum Bend Radius		Weight	
	in	mm	in	mm	in	mm	in	mm	lbs/ 100 ft	kg/ 100 m
	4262-3010	3/16	4.8	.377	9.6	.090	2.3	.75	19.1	3.3
4262-4010	1/4	6.6	.445	11.3	.085	2.2	.75	19.1	4.6	6.8
4262-4020	1/4	6.4	.460	11.7	.098	2.4	.75	19.1	5.0	7.4
4262-5030	5/16	7.9	.527	13.4	.100	2.5	.87	22.1	6.1	9.0